

# Model MK 56 | Dynamic climate chambers for rapid temperature changes

The BINDER MK series chamber is suitable for all heat and cold tests between -40 °C and 180 °C. The MK is a clever alternative to complex individual solutions for cyclical temperature tests.

# BENEFITS

- Homogeneous climate conditions thanks to APT.line<sup>™</sup> technology
- · Comprehensive programming and data acquisition
- Large heated viewing window



Model 56

## MAIN FEATURES

- Temperature range: -40 °C to 180 °C
- APT.line<sup>™</sup> preheating chamber technology
- Programmable condensation protection for test material
- Heated viewing window with LED interior lighting
- BINDER APT-COM<sup>™</sup> 3 Basic Edition communication software
- Troubleshooting system with visual and audible alarms
- Intuitive touchscreen controller with time-segment and real-time programming with internal data recording
- · Access port with silicone plug, 50 mm, left
- · 4 castors, two with brakes
- Computer interface: Ethernet
- Adjustable ramp function

#### · Integrated chart recorder

- Real-time clock
- · 1 stainless steel rack
- · BINDER test confirmation
- · Inner chamber made of stainless steel
- Pt 100 temperature sensor
- Thermal insulation using PUR foam
- CFC-free refrigerant R-404A
- Cooling with compressor cooling unit
- Fin evaporator

# ORDERING INFORMATION

Interior volume [cu.ft.]	Voltage	Option model	Version	ArtNo.
Model MK 56				
2.1	200230 V 1 ph 50 Hz	Standard	MK056-230V	9020-0316
	200240 V 1 ph 60 Hz	Standard	MK056-230V	9020-0395

# Authorized UK and Ireland Distributor:



#### Address

Instruments 4 Engineers Ltd Business & Innovation Centre Broadstone Mill, Broadstone Road Stockport SK5 7DL, United Kingdom

# Contact

Tel: +44 (0) 161 871 7450 sales@instruments4engineers.com





# **TECHNICAL DATA**

Description	MK056-230V1	MK056-230V <sup>1</sup>
Article Number	9020-0316	9020-0395
Performance Data Temperature		
Temperature range [°C]	-40180	-40180
Temperature variation depending on setpoint [± K]	0.51.5	0.51.5
Temperature fluctuation depending on setpoint [± K]	0.10.5	0.10.5
Average heating-up rate according to IEC 60068-3-5 [K/min]	5.5	5.5
Cooling down time from 180 °C to -40 °C [min]	90	90
Average cooling down time according to IEC 60068-3-5 [K/min]	5.5	5.5
Max. heat compensation at 25 °C [W]	800	800
Electrical data		
Rated Voltage [V]	200230	200240
Power frequency [Hz]	50	60
Nominal power [kW]	2.8	2.8
Unit fuse [A]	16	16
Phase (Nominal voltage) [ph]	1	1
Outer dimensions		
Width net [mm]	720	720
Height net [mm]	1445	1445
Depth net [mm]	780	780
Wall clearance back [mm]	300	300
Wall clearance sidewise [mm]	200	200
Viewing window width [mm]	288	288
Viewing window height [mm]	255	255
Doors		
Inner doors	1	1
Unit doors	1	1
Internal Dimensions		
Width [mm]	400	400
Height [mm]	420	420
Depth [mm]	348	348
Measures		
Interior volume [L]	60	60
Net weight of the unit (empty) [kg]	165	165
permitted load [kg]	60	60
Load per rack [kg]	15	15
Environment-specific data		
Sound-pressure level [dB(A)]	59	59
Fixtures		
Number of shelves (std./max.)	1/4	1/4

1 All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.



### Address


Instruments 4 Engineers Ltd Business & Innovation Centre Broadstone Mill, Broadstone Road Stockport SK5 7DL, United Kingdom

#### Contact


Tel: +44 (0) 161 871 7450 sales@instruments4engineers.com



# DIMENSIONS incl. fittings and connections [mm]



# CHARTS



Heat compensation chart

# OPTIONS AND ACCESSORIES

Designation	Description	*	ArtNo.
Access port with silicone plug	left		
	30 mm	01	8012-1322
	50 mm	01	8012-1328
	80 mm	01	8012-1334
	right		
	30 mm	01	8012-1319
	50 mm	01	8012-1325
	80 mm	01	8012-1331
	top		
	80 mm	01	8012-1536
Analog output 4-20 mA	for temperature values (output not adjustable)	-	8012-1084
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	-	8012-1124
Calibration certificate, temperature	for temperature, measurement in center of chamber at specified temperature	-	8012-1143
	temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-1602
	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-1581
	temperature measurement incl. certificate, 9 measuring points at specified temperature	-	8012-1560
Data Logger Kit	T 220: For continuous temperature logging from -90 °C to 220 °C. The kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit	19	8012-0715
Data Logger Software	LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)	19	8012-0821

\* Notes > See last page

Data Sheet Model MK 56

# BINDER

Designation	Description	*	ArtNo.
Door lock	lockable door handle	-	8012-1782
Dry-air purge, connection	for the connection to an existing pressurized air network	-	8012-1795
Interface converter	RS 422 cable set and RS 232 / RS 422 interface converter for connection to 10-way plug distributor or for connection to a unit		
	120 V, 60 Hz option model	-	8012-0557
	230 V, 50/60 Hz option model	-	8012-0556
	RS 422 cable set and RS 422 / Ethernet interface converter for connection to 10-way plug distributor or for connection to a unit		
	120 V, 60 Hz option model	-	8012-0405
	230 V, 50/60 Hz option model	-	8012-0380
Interface converter, USB / RS422	RS 422 cable set and RS 422 / USB interface converter for connection to 10-way plug distributor or for connection to a unit (USB-powered converter)	-	8012-0665
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-0016
Pt 100 temperature sensor	additional flexible Pt 100, interior, for displaying the temperature on the unit display	-	8012-1093
Rack accessories	Rack accessories – fasteners (1 set of 4) for additional security of racks	-	8012-1092
Rack, reinforced	stainless steel, with fasteners (1 set of 4), max. load 70 kg	-	8012-1091
Racks	stainless steel	-	6004-0150
	modular plug distributor for 10 RS 422 interfaces	-	8012-0295
RS 422 interface, accessories	RS 422 connection cable (15 m) between plug distributor and RS 422 interface	-	5023-0036
	RS 422 extension cable (50 m) between interface converter and unit or RS 232 / RS 422 plug distributor	-	5023-0117
RS 485, 2-wire	Additional serial interface can be used parallel to Ethernet, for communication software	-	8012-1768
Shelf, perforated	Stainless steel	-	6004-0182
	APT-COM™ communications software		
	version 2 to 3, GLP edition	19	9053-0016
	version 3, BASIC edition	19	9053-0014
Software	version 3, GLP edition	19	9053-001
	version 3, STANDARD edition	19	9053-001
	APT-COM™ communications software, price: for free		
	version 3, GLP DEMO Edition	19	9053-0008
Temperature safety device class 2	with visual alarm (DIN 12880)	-	8012-179
Zero voltage relay contacts	for controlling 3 relay contacts via program regulators, accessible via 6-pin DIN socket (max. 24 V - 2.5 A)	-	8012-109

\* Notes > See last page

# SERVICES

Designation	Description	*	ArtNo.
Installation services			
Installation	and set up of unit at operating location, connect to existing connections	13, 18	DL10-0100
Instruction	unit function instructions for operation and programming of the controller	18	DL10-0600
Preventive maintenance			
Preventive maintenance	Executive of equipment inspection according to maintenance plan	14, 18	DL20-0300
Calibration services			
Calibration temperature incl. certificate	including certificate, one measuring point in center of chamber at specified temperature	14, 16, 17, 18	DL30-0101
Temperature measurement 18 measuring points	including certificate, 18 measuring points at specified temperature	14, 16, 17, 18	DL30-0118
Temperature measurement 27 measuring points	including certificate, 27 measuring points at specified temperature	14, 16, 17, 18	DL30-0127
Temperature measurement 9 measuring points	including certificate, 9 measuring points at specified temperature	14, 16, 17, 18	DL30-0109



#### Address

Instruments 4 Engineers Ltd Business & Innovation Centre Broadstone Mill, Broadstone Road Stockport SK5 7DL, United Kingdom

#### Contact

Tel: +44 (0) 161 871 7450 sales@instruments4engineers.com



Designation	Description	*	ArtNo.
Validation services			
Execution of IQ/OQ	in accordance with qualification folder	15, 18, 20	DL41-0200
Execution of IQ/OQ/PQ	in accordance with customer's requirement, price: on request	15, 18	DL44-0500
Qualification folder IQ/OQ	supporting documents for validation performed by customer, consisting of: IQ/OQ checklists, unit schematics, QM certificate in accordance with ISO 9001	15, 18, 20	8012-0863
Qualification folder IQ/OQ/PQ	supporting documents for validation performed by customer, in accordance with customer's requirement, extension of Qualification folder IQ/OQ by chapter PQ	15, 18	8012-0951
Warranty service			
Extension of the warranty from 2 to 3 years	beginning with the date of delivery, wearing parts are not included	-	DL01-1041
Extension of the warranty from 2 to 5 years	beginning with the date of delivery, wearing parts are not included	_	DL01-1042

\* Notes > See last page



#### Address

Instruments 4 Engineers Ltd Business & Innovation Centre Broadstone Mill, Broadstone Road Stockport SK5 7DL, United Kingdom

#### Contact

Tel: +44 (0) 161 871 7450 sales@instruments4engineers.com



### NOTES

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. 01 02
- UL mark is not granted when this option is used. Heat resistant only to max. 200 °C.
- 03
- Only available on units rated for 230 V. 04
- 06 Heating-up time may increase as a result of the lower heat conductivity.
- 07 The additional heat input may affect the temperature behavior. Not in conjunction with the optional access port, door with window and interior lighting. 09
- 10 11 12 Not available on 23-liter units.
- Not available on 23- or 53-liter units.
- Only available on units rated for 230 V or 400 V.
- 13 Installation and connections take place at unit location; transport within the company only upon consultation.
- 14 We recommend a BINDER service contract to cover unit inspections, calibrations and validations.
- 15 OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- Sensor calibration is performed in an accredited calibration laboratory. 16
- 17
- Calibration is performed according to the BINDER factory standard. Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not 18 include a country-specific added fee (available on request).
- For additional accessories, refer to the Process documentation chapter. 19
- 20 When ordering IQ/OQ qualification folders and associated IQ/OQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ folder. When ordering IQ/OQ/PQ qualification folders and associated IQ/OQ/PQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ/PQ folder.